

Easy Scale Link

No setting is required between **Uniwell POS** and **DS-980SC Uniwell Version**.
You can use the scale immediately after the cable is connected.

Uniwell POS



DIGI Scale DS-980SC Uniwell Version



RS-232C



Connectable Uniwell POS

DX-890 / TX-870 / SX-series / PX-series /
EX-series / LX-series

Scale Specification

| | |
|------------------------|--|
| Capacity | 15 kg or 30 lb |
| Interface | RS-232C |
| Protocol | Uniwell, ICL old Omron (Type Q) V1.05 or later |
| Interface Cable | 24CNW00PC16400 (option) |
| Power Source | DC12V/1W |
| Size (mm) | Remote Display: 167.6(W) x 101.3(D) x 399.5(H) Scale: 341(W) x 284(D) x 80(H) |



Uniwell Corporation
<http://www.uniwell.com>

5-25, 3-chome, Tenma, Kita-ku,
Osaka, JAPAN, 530-0043
Tel : 81-6-6353-7021
Fax : 81-6-6352-7104
E-mail : contact@uniwell.com



TERAOKA SEIKO CO., LTD.
<http://www.digisystem.com>

Shanghai Teraoka Electronic Co., Ltd.
Ting Lin Industry Developmental Zone,
Jin Shan Country, Shanghai 201505 China
Tel : 86-21-5723-4888
Fax : 86-21-5723-9330
E-mail : steservice@dig-scale.com